


# Model THS15 Heat Sealer

Quickly creates durable seals on large, plastic mattress bags or similar wraps at a cost-effective price!

We can customize the jaw separation (7in is standard; up to 18in is available)



Using the THS15 w/ a Bagging Table

## Specifications

- Seals up to 10mil-thick poly bags in 8-15sec
- 84in sealing length (custom lengths available)
- Bed height adjustable from 30-40in above floor
- 7in sealing jaw separation (custom separations up to 18in available)
- Single 1/8in-wide seal (different widths or dual-band seals available)
- Heavy-duty foot switch initiates sealing process
- LCD screen and keypad used to access seal/cool times, piece counter, and control options
- Safety controls detect obstructions in jaws
- Lockable UL489-rated disconnect switch
- Electrical requirements: 200-240VAC, 50/60Hz, 1-phase, 8.5FLA
- Pneumatic requirements: 80-120psi, 3cfm

## Operation

1. Bag the mattress.
2. Pull the open end of the bag between the sealing jaws.
3. Hold down the foot pedal until the jaws clamp down on the bag
4. Release the foot pedal and wait while the seal is formed.
5. Pull off the excess plastic to trim the bag (if desired).
6. Sealer automatically resets the upper jaw to the starting position when the seal is complete.



5559 National Turnpike, Louisville, KY 40214 USA  
Phone: (502)366-0407 Fax: (866)927-9034  
Email: [info@drcashinc.com](mailto:info@drcashinc.com) Web: [www.drcashinc.com](http://www.drcashinc.com)

Mattress Bag Heat Sealers